



Part Number	UNITWA1.5BK/RD1250B
Description	UniStrand Black/Red Thin Wall Automotive Cable
Conductor Material	Bare copper
Insulation	PVC
Insulation Radial Thickness	0.4mm *Average
Outer Diameter	2.40±0.10MM
Conductor Stranding	30/0.25±0.008 MM
Conductor Cross Section Area	1.5mm ²
Voltage Rating	60V
Cable Weight	23kg per box
Temperature Range	Max 70 °C
Length Supplied	500m +/- 10-12%
Applicable Standards	ISO6722

