


CLIFF

USB3.0 B-A EARTHED METAL FEEDTHROUGH CONNECTOR



Feedthrough Features

- Fits standard XLR Ø24mm cutout.
- No soldering or punch termination. Use standard cable for each connector style.
- Front or rear mounted.

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

VARIANTS

Part No.

CP30107 - USB3.0 B-A Female Metal Earthed Feedthrough Nickel CSK hole

CP30109 - USB3.0 B-A Female Metal Earthed Feedthrough Black CSK hole

Material

1. Metal Frame: Diecast, Black or Nickel plated
2. USB Connector: PBT
3. USB Contacts: Gold plated
4. Contacts: Brass, Tin or Nickel plated

Notes

Contact Resistance: $\leq 30\text{m}\Omega$

Dielectric Strength: 500V AC

Insulation Resistance :1000M Ω

Operating Temperature: -25°C to +85°C

Rated Current: 1.5A

Rated Voltage: 30V

Lifetime: >1500 mating cycles