






REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------





SECTION A-A

NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
2. PITCH: 5.08MM POLES: 2P-16P
- 3.RATED VOLTAGE/CURRENT: UL 300V/10A
VDE 320V/20A
- 4.OPERATION TEMPERATURES: -40° C~+105° C
- 5.RATED IMPULSE VOLTAGE: AC2500V
- 6.INSULATION RESISTANCE: 5000M Ω /DC1000V
- 7.WIRE RANGE: 26~12AWG 0.2~2.5MM²
- 8.UNDIMENSIONED TOLERANCES:

Pitch range in mm		Nominal dimension range in mm						
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150	—
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	□



1	2EDGKD-5.08-Housing	1085A0YXXA (H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES

DETACHED LISTS		DEGSON®			
TOLERANCES EXCEPT AS NOTED		NAME:			
.X ± .XX ± .XXX ±		2EDGKD-5.08-XXP-1Y-00A(H)			
ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING	
THIRD ANGLE PROJECTION		CHKD:		DRAWING NO.: 2EDGKD-5.08-E01	
		DRFT: Haoyh 06/27/05"		DO NOT SCALE DRAWING	SCALE N/A
				SHEET	1/1

5	2EDGKD-5.08-Spring	X000004810 (H)	XX	Stainless steel	
4	2EDGKD-5.08-Clamp	1085B00010 (H)	XX	Phosphor bronze	Sn plated
3	2EDGKD-5.08-Button	1085D0501A (H)	XX	PA66	UL94V-0
2	2EDGKD-5.08-Cover	1085C0YXXA (H)	1	PA66	UL94V-0