




REV	ECN	DESCRIPTION	DRFT	DATE
▲		Drawing emend	CSX	04/21/06"
▲		增加VDE、CE标志	Yej	02/27/08"
▲		图面更新	Yej	03/28/08"
▲		增加自动化方针	WLM	09/23/08"
▲	10-0329	增加标注尺寸	COCO	10/04/10"
▲	14-0107	黄铜支撑架, 将号变更: 工频耐压变	WL	06/26/14"




**DEGSON**  
-5.08  
2EDGRC

NOTES:

1. DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
2. PITCH: 5.08MM, POLES: 2-24P
3. RATED VOLTAGE/CURRENT: UL 300V/15A VDE 320V/20A
4. OPERATION TEMPERATURES: -40°C~+105°C
5. RATED IMPULSE VOLTAGE: 4.0KV ▲
6. INSULATION RESISTANCE: 5000MΩ/DC1000V
7. UNDIMENSIONED TOLERANCES:

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES	Pitch range in mm	Nominal dimension range	—					
						over 6 to 10	over 10 to 14	over 14 to 20	over 20 to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150
1	2EDGRC-5.08-Housing	1009A0YXXA(H)	1	PA66	UL94V-0	±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0

1. DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
2. PITCH: 5.08MM, POLES: 2-24P
3. RATED VOLTAGE/CURRENT: UL 300V/15A VDE 320V/20A
4. OPERATION TEMPERATURES: -40°C~+105°C
5. RATED IMPULSE VOLTAGE: 4.0KV ▲
6. INSULATION RESISTANCE: 5000MΩ/DC1000V
7. UNDIMENSIONED TOLERANCES:



P.C.B LAYOUT

DETACHED LISTS		MATERIAL		NOTES	
tolerances except as noted					
X ± XX ± XXX ±	X' ± XX' ± XXX' ±				
ANGLES ± 1°	APP'D:				
THIRD ANGLE PROJECTION	CHKD:				
	DEFT: HW 08/23/05"	DRAWING NO.: 2EDGRC-5.08-E06	REV	T6	A
	DO NOT SCALE DRAWING	SCALE	N/A	SHEET	1/1