

D1RFRD006

7

6

5

4

3




2

1


REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

VIEW B




SEC A-A



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.08MM,POLES: 2-24P
- 3.RATED VOLTAGE/CURRENT:UL 300V/15A
VDE 320V/20A
- 4.OPERATION TEMPERATURES: -40°C~+105°C
- 5.RATED IMPULSE VOLTAGE: 4.0KV
- 6.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 7.UNDIMENSIONED TOLERANCES:

Pitch range in mm		Nominal dimension range in mm							
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150		
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10	



P.C.B LAYOUT

2	2EDGV-Pin header Automatic assembly	1007B00340(H)	XX	COPPER	Sn Plated
2	2EDGV-Pin header Manual assembly	1007B00330(H)	XX	COPPER	Sn Plated
1	2EDGVC-5.08 Housing	1009A0YXXA(H)	1	PA66	UL94V-0

DETACHED LISTS	ITEM		NAME OF PART		NO. OF PART		QTY		MATERIAL		NOTES	
	MM (INCH)		MATERIAL:		DEGSON®							
	TOLERANCES EXCEPT AS NOTED		FINISH:									
	.X ± .XX ± .XXX ±		.X" ± .XX" ± .XXX" ±		PART NO.:		NAME: 2EDGVC-5.08-XXP-1Y-00A(H)					
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING						REV	T5
			CHKD:		DRAWING NO.: 2EDGVC-5.08-E06							
	THIRD ANGLE PROJECTION		DRFT: HW 08/23/05"		DO NOT SCALE DRAWING		SCALE	N/A	SHEET	1/1		

DETACHED LISTS

MM
(INCH)

TOLERANCES EXCEPT AS NOTED

.X ±
.XX ±
.XXX ±.X" ±
.XX" ±
.XXX" ±

ANGLES ± 1°

THIRD ANGLE PROJECTION

MATERIAL:

FINISH:

PART NO.:

APPD:

CHKD:

DRFT: HW 08/23/05"

NO. OF PART

Q'TY

NAME:

TITLE: ASSEMBLY DRAWING

DRAWING NO.: 2EDGVC-5.08-E06

DO NOT SCALE DRAWING

MATERIAL

FINISH:

PART NO.:

APPD:

CHKD:

DRFT: HW 08/23/05"

NOTES

NAME:

TITLE: ASSEMBLY DRAWING

DRAWING NO.: 2EDGVC-5.08-E06

DO NOT SCALE DRAWING

SCALE N/A