



REVISION RECORD




REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------





NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.08MM ,POLES: 4P-XXP
- 3.RATED VOLTAGE/CURRENT:UL 300V/12A
VDE 250V/15A
- 4.OPERATION TEMPERATURES: -40℃~+105℃
- 5.WITHSTANDING VOLTAGE: AC2000V/1MIN
- 6.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 7.WIRE RANGE: 26-14AWG,0.5-1.5MM²
- 8.MAX.TORQUE VALUE: M2.5,4.08KGF.CM
- 9.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm						
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150		
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10	



A-A



3	DG127A-5.08-Pin	4107B00010(H)	xx/2	Brass	SnCe plated
2	DG127 Cage	X000000170(H)	XX	Brass	Ni plated
1	DG127A-5.08-Housing	4107A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES

DETACHED LISTS	MM (INCH)		MATERIAL:		 DEGSON ®					
	TOLERANCES EXCEPT AS NOTED		FINISH:							
	.X ± .XX ± .XXX ±		.X' ± .XX' ± .XXX' ±		PART NO.:		NAME: DG127A-5.08-XXP-1Y-001(H)			
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING				REV	T2
			CHKD:		DRAWING NO.: DG127-5.0-E01					
	THIRD ANGLE PROJECTION		DRFT: Zhuwm 04/23/08"		DO NOT SCALE DRAWING		SCALE	N/A	SHEET	1/1

5	DG127 "—"Screws	S000001450(H)	XX	Steel	Cr ³ Zn
4	DG127-5.08-Pin	4028B00010(H)	XX/2	Brass	SnCe plated