


REVISION RECORD				
REV	ECO	DESCRIPTION	DRT	DATE
Δ		PA66-25%GF 代替原PBT材料	H80yh	85/18/11
Δ		PA66+10%GF 代替PA66+25%GF	WfE	88/12/88*
Δ	15-0138	修改针头部尺寸	ZMT	87/07/12*



Notes:

1. Rated voltage: 300V
2. Rated current: 10A
3. Insulation resistance: 5000M Ω /DC1000V
4. Withstanding voltage: AC1500V/1Min
5. Temp. Range: -40° C~+105° C
6. Undimensioned Tolerances:

Pitch range in mm		Nominal dimension range in mm		
over 6	over 10	over 6	over 30	over 90
to 10	to 24	to 6	to 30	to 200
to 10		to 6	to 90	to 480
±0.10	±0.15	±0.25	±0.1	±0.2±0.3±0.5±0.7

2	DG332-Pin header	4014B0010(H)	XX	Brass	Since
1	DG332J-5.0-Housing	4014A0YXXA(H)	1	PA66+10%GF	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
DETACHED LISTS					
TOLERANCES EXCEPT AS NOTED					
MM	0.0 ±	±	±	±	±
MM	0.00 ±	±	±	±	±
MM	0.00 ±	±	±	±	±
ANGLES ± 1°					
THIRD ANGLE PROJECTION					
SCALE : 1:1					
DO NOT SCALE DRAWING					
SHEET 1 OF 1					