




REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------



NOTES:

- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
- 2.PITCH: 5.0MM ,POLES: N=2-24P
- 3.RATED VOLTAGE/CURRENT:UL 300V/10A
VDE 250V/12A
- 4.INSULATION RESISTANCE: 5000MΩ/DC1000V
- 5.WITHSTANDING VOLTAGE: AC2000V/1MIN
- 6.TEMP.RANGE: -40 ° C~+105 ° C
- 7.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm						—
to	over 6 to 10	over 10 to 24	to 6	over 6 to 30	over 30 to 90	over 90 to 200	over 200 to 480		
±0.10	±0.15	±0.25	±0.1	±0.2	±0.3	±0.5	±0.7	0.05/10	

2	DG332-Pin header	4014B00010(H)	XX	Brass	Sn Plated
1	DG332J-5.0-Housing	4014AYYXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES

DETACHED LISTS	MM (INCH)	MATERIAL:	DEGSON®		
	TOLERANCES EXCEPT AS NOTED	FINISH:			
	.X ± .XX ± .XXX ±	.X" ± .XX" ± .XXX" ±	PART NO.:	NAME: DG332J-5.0-XXP-1Y-00A(H)	
	ANGLES ± 1°	APPD:	TITLE: ASSEMBLY DRAWING		REV
THIRD ANGLE PROJECTION		CHKD:	DRAWING NO.: DG332J-5.0-E05		T4
DRFT: Haoyh 05/12/05"		DO NOT SCALE DRAWING	SCALE	1:1	SHEET 1/1