

DATASHEET - FL2-2



Flange, knockout 10x M16, 3x M20, HxWxD=116x187.5x23mm



Part no. FL2-2
Catalog No. 017898
EL-Nummer (Norway) 0004132127

Delivery program

Product range			xEnergy Safety Ci
Basic function			Basic enclosures
Product function			Accessories for basic enclosures
Accessories			Flanges
Single unit/Complete unit			Modular system
Description			sponge-rubber, captive gasket Quick mounting using wedge-lock fasteners (included as standard)
For use with enclosure dimensions			187.5 mm
Cable entry			10 x M16, 3 x M20

Technical data ETIM 7.0

Distribution boards (EG000023) / Gland plate for small distribution boards/switchgear cabinets (EC000211)			
Electric engineering, automation, process control engineering / Electrical installation, device / Electrical distribution system (incl. small distribution board) / Gland plate for small distribution boards/switchgear cabinets (ecl@ss10.0.1-27-14-24-21 [ADI315007])			
Model			Cable screw gland
Type			Straight
Width		mm	142
Height		mm	116
Depth		mm	23
Material			Plastic
Surface protection			Untreated
Degree of protection (NEMA)			Other
Pre-stamping			Yes
Number of connector holes			0
Thread type			Metric
Suitable for nominal thread metric/PG			16 - 20

Dimensions

