

DATASHEET - FL4-X



Flange, closed, HxWxD=116x329x23mm



Part no. FL4-X
Catalog No. 024355

EL-Nummer 4132328
(Norway)

Delivery program

Product range			xEnergy Safety Ci
Basic function			Basic enclosures
Product function			Accessories for basic enclosures
Accessories			Flanges
Single unit/Complete unit			Modular system
Description			sponge-rubber, captive gasket Quick mounting using wedge-lock fasteners (included as standard)
For use with enclosure dimensions			375 mm
Cable entry			Drill as required

Technical data ETIM 7.0

Distribution boards (EG000023) / Gland plate for small distribution boards/switchgear cabinets (EC000211)

Electric engineering, automation, process control engineering / Electrical installation, device / Electrical distribution system (incl. small distribution board) / Gland plate for small distribution boards/switchgear cabinets (ecl@ss10.0.1-27-14-24-21 [ADI315007])

Model			Blind
Type			Straight
Width		mm	329
Height		mm	116
Depth		mm	23
Material			Plastic
Surface protection			Untreated
Degree of protection (NEMA)			Other
Pre-stamping			No
Number of connector holes			0
Thread type			None
Suitable for nominal thread metric/PG			16 - 50

Dimensions

