

DATASHEET - FL4-D



Flange, through-hole foam rubber, IP54, HxWxD=116x329x23mm



Part no. **FL4-D**
 Catalog No. **044879**
 EL-Nummer (Norway) **0002502207**

Delivery program

Product range			xEnergy Safety Ci
Basic function			Basic enclosures
Product function			Accessories for basic enclosures
Accessories			Sponge-rubber flange IP54
Single unit/Complete unit			Modular system
Protection type			IP54
For use with enclosure dimensions			375 mm
For use with			NYY, NYM 3 x 1.5 mm ² - 5 x 2.5 mm ² NYY, NYM 4 x 4 mm ² - 5 x 10 mm ² NYY, NYM 4 x 10 mm ² - 4 x 50 mm ²
Outer cable diameter		mm	42 x 10 - 13 4 x 15 - 19 2 x 20 - 30

Technical data ETIM 7.0

Distribution boards (EG000023) / Gland plate for small distribution boards/switchgear cabinets (EC000211)

Electric engineering, automation, process control engineering / Electrical installation, device / Electrical distribution system (incl. small distribution board) / Gland plate for small distribution boards/switchgear cabinets (ecl@ss10.0.1-27-14-24-21 [ADI315007])

Model			Cable screw gland
Type			Straight
Width		mm	375
Height		mm	120
Depth		mm	23
Material			Plastic
Surface protection			Untreated
Degree of protection (NEMA)			Other
Pre-stamping			Yes
Number of connector holes			0
Thread type			None
Suitable for nominal thread metric/PG			0 - 0

Dimensions



