


SPECIFICATION:

Current rating: 5 A
 Voltage rating: 24 V DC
 Insulation resistance: 100 MΩ min. at 500 V DC
 Contact resistance: 30 mΩ max.
 Dielectric voltage: 500 V AC
 Insertion Force: 0.3~3.0 kg
 Extraction Force: 0.3~3.0 kg
 Operating life: 5000 Mating cycles

RoHS
COMPLIANT




MATERIAL:

Housing: PBT
 Barrel: Brass
 Terminal: Brass

FINISH:

Barrel: Nickel plated
 Terminal: Silver plated



Order-Information

Identifier:

DCE4A

DC Socket angled PCB mount, Pin 2.0 mm