





No.	Changes and/or Note No.	Date	Sign	No.	Changes and/or Note No.	Date	Sign




UNC #4-40 Hexscrew



HGCF 15M/F GENDER CHANGER
PIN OUT: 15Male

15Female



Label: yellow color with black character

One side: MINI GENDER CHANGER

The other side: U.S.A. PATENT 5199906 (GENDER CHANGER)

SPECIFICATION

INSULATOR: PBT Glass fibre reinforced UL 94 VO

CONTACT: Brass

CONTACT PLATING: Gold plated over nickel

SHELL: Tin plated shell

CURRENT RATING: 3 AMP

DIELECTRIC STRENGTH: 1000V AC for one minute

INSULATOR RESISTANCE: 1000MΩ min at 500V DC

TEMPERATURE: -55°C → +105°C

DATE	26/11/2012	DRAWN	SCALE	MATERIAL TYPE		
		APPROVED		REPLACES		
		GENDER CHANGER - High Density Male to Female DMGC-HDxxxx-MF				
					DRAWING No.	