

D-Sub Plastic Cover, Top cable entry

TECHNICAL SPECIFICATIONS


Material:	UL 94 V-0 Plastic Material	
Operating Temperature:	-55°C to +110°C	
Cable Entry:	Top	
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request	
Cable O.D.:	9-way	Up to 11,7mm
	15-way	Up to 11,7mm
	25-way	Up to 11,7mm
	37-way	Up to 11,7mm
Colour:	Black	



Features:

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Strain relief inserts ensure a secure termination
- Re-openable
- Also available in Metalized and Full Metall version

Grommet Sizes DTPK-P:



Size DTPK-P	Dim A	Dim B	Dim C
9-way	31,2	39,9	15,0
15-way	39,5	41,5	15,0
25-way	53,4	48,6	15,0
37-way	69,7	53,6	15,0

Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-0108-01	DTPK-P-09-BK-K
15-way	6560-0108-02	DTPK-P-15-BK-K
25-way	6560-0108-03	DTPK-P-25-BK-K
37-way	6560-0108-04	DTPK-P-37-BK-K

Size:	P/N - BULK:	Product Code:
9-way	6561-0108-01	DTPK-P-09-BK
15-way	6561-0108-02	DTPK-P-15-BK
25-way	6561-0108-03	DTPK-P-25-BK
37-way	6561-0108-04	DTPK-P-37-BK

