

D-Sub Full Metal, Top cable entry with Metalized Grommet Set

TECHNICAL SPECIFICATIONS

Material:	Zinc, Nickel Plated
Operating Temperature:	-40°C to +120°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request
Cable O.D:	Up to 13mm

**Multi Hood (MH) Series**


- with three options for cable entry / assembly:

- Crimp Ferrule (MHC)
- Metalized grommet (MHDM)
- Metalized Cone + Clamp (MHEE)



Features:

- Available in sizes 9-15-25-37
- 360° EMI Shielding
- Quick assembly
- Supports all types of cables
- Suitable for any common D-Sub connector

Grommet Sizes MHDM:



Size 9-15-25-37



Size:	Dim A	Dim B	Dim C
9-way	32,2	41,3	15,4
15-way	40,6	43,3	15,4
25-way	54,5	49,5	15,4
37-way	70,7	54,3	15,4

Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-0136-01	MHDM-09-K
15-way	6560-0136-02	MHDM-15-K
25-way	6560-0136-03	MHDM-25-K
37-way	6560-0136-04	MHDM-37-K

Size:	P/N - BULK:	Product Code:
9-way	6561-0136-01	MHDM-09
15-way	6561-0136-02	MHDM-15
25-way	6561-0136-03	MHDM-25
37-way	6561-0136-04	MHDM-37