

D-Sub Full Metal, Top cable entry, With C-Clip

TECHNICAL SPECIFICATIONS



Material:	Zinc, Nickel Plated
Operating Temperature:	-40°C to +120°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request
Cable O.D:	Up to 11,5mm

Features:

- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Re-openable
- Full Metal Jackscrews
- Strain relief inserts ensure a secure termination
- Metal C-Clip clamp - suitable for foil cable with earth wire / ground wire.



Grommet Sizes:



Size DTCK	Dim A	Dim B	Dim C
9-way	31,0	39,5	15,0
15-way	39,5	41,5	15,0
25-way	53,5	48,5	15,0
37-way	71,0	53,0	15,0

Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-0805-01	DTCK09-K
15-way	6560-0805-02	DTCK15-K
25-way	6560-0805-03	DTCK25-K
37-way	6560-0805-04	DTCK37-K

Size:	P/N - BULK:	Product Code:
9-way	6561-0805-01	DTCK09
15-way	6561-0805-02	DTCK15
25-way	6561-0805-03	DTCK25
37-way	6561-0805-04	DTCK37

