

Datasheet

Manufacturer Part No.: T24CA101 ... T24CA0114

Expandable PET Braided Sleeving (bulk stock)

Part-No.: T24CA101 ... T24CA114



This cable braided sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This high flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites.

The woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends.

To prevent fraying, the sleeve should be cut with a hot cutting tool!

Technical data: Material: polyester braid, high flexible (PET) • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

Part-No.	Description	Expansion range	Flat width	Selling unit	Complete reel	
					Content / max. length	EAN/GTIN
T24CA101	Expandable Braided Sleeve 1...6 mm, Black	1 ... 6 mm	4 mm	1 m +	1000 m	4260732287698
T24CA102	Expandable Braided Sleeve 4...8.5 mm, Black	4 ... 8,5 mm	6 mm	1 m +	500 m	4260732287704
T24CA103	Expandable Braided Sleeve 5...16 mm, Black	5 ... 16 mm	8 mm	1 m +	350 m	4260732287711
T24CA104	Expandable Braided Sleeve 7...19 mm, Black	7 ... 19 mm	10 mm	1 m +	350 m	4260732287728
T24CA105	Expandable Braided Sleeve 8...24 mm, Black	8 ... 24 mm	12 mm	1 m +	250 m	4260732287735
T24CA106	Expandable Braided Sleeve 10...27 mm, Black	10 ... 27 mm	16 mm	1 m +	200 m	4260732287742
T24CA107	Expandable Braided Sleeve 14...30 mm, Black	14 ... 30 mm	20 mm	1 m +	200 m	4260732287759
T24CA108	Expandable Braided Sleeve 18...35 mm, Black	18 ... 35 mm	25 mm	1 m +	200 m	4260732287766
T24CA109	Expandable Braided Sleeve 20...55 mm, Black	20 ... 55 mm	32 mm	1 m +	150 m	4260732287773
T24CA110	Expandable Braided Sleeve 30...60 mm, Black	30 ... 60 mm	38 mm	1 m +	100 m	4260732287780
T24CA111	Expandable Braided Sleeve 35...75.5 mm, Black	35 ... 75,5 mm	45 mm	1 m +	100 m	4260732287797
T24CA112	Expandable Braided Sleeve 40...80 mm, Black	40 ... 80 mm	50 mm	1 m +	100 m	4260732287803
T24CA113	Expandable Braided Sleeve 45...105 mm, Black	45 ... 105 mm	64 mm	1 m +	100 m	4260732287810
T24CA114	Expandable Braided Sleeve 63.5...120.7 mm, Black	63.5 ... 120.7 mm	76 mm	1 m +	100 m	4260732287827