

## Expandable PET Braided Sleeving (bulk stock)

### Part-No.: T24CA101 ... T24CA114



This cable braided sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This high flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites.

The woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends.

**To prevent fraying, the sleeve should be cut with a hot cutting tool!**

**Technical data:** Material: polyester braid, high flexible (PET) • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

| Part-No. | B/N - No. | Description                                      | Expansion range   | Flat width | Selling unit | Complete reel         |               |
|----------|-----------|--|-------------------|------------|--------------|-----------------------|---------------|
|          |           |  |                   |            |              | Content / max. length | EAN/GTIN      |
| T24CA101 | 3344385   | Expandable Braided Sleeve 1...6 mm, Black        | 1 ... 6 mm        | 4 mm       | 1 m +        | 500 m                 | 4260732287698 |
| T24CA102 | 3344386   | Expandable Braided Sleeve 4...8.5 mm, Black      | 4 ... 8,5 mm      | 6 mm       | 1 m +        | 500 m                 | 4260732287704 |
| T24CA103 | 3344387   | Expandable Braided Sleeve 5...16 mm, Black       | 5 ... 16 mm       | 8 mm       | 1 m +        | 350 m                 | 4260732287711 |
| T24CA104 | 3344388   | Expandable Braided Sleeve 7...19 mm, Black       | 7 ... 19 mm       | 10 mm      | 1 m +        | 350 m                 | 4260732287728 |
| T24CA105 | 3344389   | Expandable Braided Sleeve 8...24 mm, Black       | 8 ... 24 mm       | 12 mm      | 1 m +        | 250 m                 | 4260732287735 |
| T24CA106 | 3344390   | Expandable Braided Sleeve 10...27 mm, Black      | 10 ... 27 mm      | 16 mm      | 1 m +        | 200 m                 | 4260732287742 |
| T24CA107 | 3344391   | Expandable Braided Sleeve 14...30 mm, Black      | 14 ... 30 mm      | 20 mm      | 1 m +        | 200 m                 | 4260732287759 |
| T24CA108 | 3344392   | Expandable Braided Sleeve 18...35 mm, Black      | 18 ... 35 mm      | 25 mm      | 1 m +        | 200 m                 | 4260732287766 |
| T24CA109 | 3344393   | Expandable Braided Sleeve 20...55 mm, Black      | 20 ... 55 mm      | 32 mm      | 1 m +        | 150 m                 | 4260732287773 |
| T24CA110 | 3344394   | Expandable Braided Sleeve 30...60 mm, Black      | 30 ... 60 mm      | 38 mm      | 1 m +        | 100 m                 | 4260732287780 |
| T24CA111 | 3344395   | Expandable Braided Sleeve 35...75.5 mm, Black    | 35 ... 75,5 mm    | 45 mm      | 1 m +        | 100 m                 | 4260732287797 |
| T24CA112 | 3344396   | Expandable Braided Sleeve 40...80 mm, Black      | 40 ... 80 mm      | 50 mm      | 1 m +        | 100 m                 | 4260732287803 |
| T24CA113 | 3344397   | Expandable Braided Sleeve 45...105 mm, Black     | 45 ... 105 mm     | 64 mm      | 1 m +        | 100 m                 | 4260732287810 |
| T24CA114 | 3344398   | Expandable Braided Sleeve 63.5...120.7 mm, Black | 63.5 ... 120.7 mm | 76 mm      | 1 m +        | 100 m                 | 4260732287827 |