




PLATING

1µ Ni + 0.4µmini Or

Part number	SEE TABLE
-------------	-----------

8630-3098NLF	Power contact #8	4.40	5.00	3.90	8.98
8630-3056NLF	Power contact #12	2.80	3.65	2.40	3.18
8630-3060NLF	Power contact #14	2.10	3.00	1.70	1.91
8630-3064NLF	Power contact #16	1.70	2.60	1.50	1.34
part numbers	Designation	ØA ^{+0.10} ₀	ØB ^{+0.10} ₀	Ø ame mm	Section mm²
CABLE					

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS06-0022	MPE	2006/03/11
B	LS06-0095	LGO	2006/06/23
C	F11-0326	APA	2011/10/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com

surface
ISO 1302

tolerance std
ISO 406 ISO 1101

projection
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

Dr M.PESSON 2006/03/11

Eng M.PESSON 2006/03/11

Chr LEGARRE 2006/03/11

Appr LEGARRE 2006/03/11

ANGULAR

LINEAR

0.XX ± 2°

0.X ± 0.1

0.XX ± 0.1

0.XXX ± 0.1

size A3

Scale 5

ECN F11-0326

Product family

D-SUB

Spec ref -

FCI

title PIN POWERS CONTACTS

catalog no

dwg no C01-8639-2160

Rev. C

CUSTOMER

sheet 1 of 1



Copyright FCI.