



FCIconnect.com

Copyright FCI

1

2




3

4

5

6

2 Screws for sizes 9&15, 3 for other sizes



MATERIAL:

thermoplastic

TEMPERATURE RANGE:

—Climatic category

—55°/ +95°

PACKAGING:


Box of 50 individual sets

Tie—Wrap



CLAMP FOR SIZES
25, 37 & 50

CLAMP FOR
SIZES 9 & 15



Bill of material		
components	Hood kit	Kit for 2 exit use
1/2 Hood	2	0
Screw	2	2
Tapping Screw	3	0
Tie Wrap	1	1
Clamp	1	1


Shell size	Number of contacts	A±0.3	B±0.3	C±0.3	With clamp			Whithout clamp		PART NUMBER	
					D±0.2	E		F±0.5	G±0.5	Black hood	Kit for 2 exit use *
						mini	maxi				
E	09	29.80	15.50	24.25	6.00	0.25	10.30	8.00	11.70	863093C09ALF	863093CEALF
A	15	29.80	15.50	32.50	6.00	0.25	10.30	8.00	11.70	863093C15ALF	
B	25	46.80	15.50	46.00	13.90	2.30	10.30	16.20	11.70	863093C25ALF	863093CBCLF
C	37	46.80	15.50	60.50	13.90	2.30	10.30	16.20	11.70	863093C37ALF	
D	50	48.80	18.00	56.50	15.60	3.90	12.60	18.00	14.00	863093C50ALF	863093CDLF

Dimensions are in millimeters

* additional accessories to be ordered separately

NOTE: RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-47-0004.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

mat'l. code				surface		tolerance		projection		product family											
—				ISO 1302		ISO 406 ISO 1101				D—SUB											
ltr	ecn no	dr	date	tolerances unless otherwise specified								title									
H	ELX-I-15087	MP	2013/06/27	angles	linear	.X±0.3						UNIVERSAL PLASTIC HOOD									
J	ELX-I-15253	MP	2013/07/16			.XX±0.1															
—	—	—	—			*±2*						scale 2									
D	LS07-0321	MPE	2007/12/19	dr	MITHUN PAUL		2013/06/27				dwg no				sheet 1 of 1				size		
E	I09-0117	AMR	2009/06/26	engr	MITHUN PAUL		2013/06/27				C01-8655-1617				A3						
F	I09-0161	AMR	2009/08/13	chr	MITHUN PAUL		2013/07/16														
G	I11-0091	AMR	2011-05-14	appd	BIJU K PAUL		2013/07/16				type CUSTOMER Drawing										
sheet index		revision		J																	
		sheet		1																	