





2	8630-CH25UNCLF	UNC 440
1	8630-CH25M3LF	M3
SL.NO.	PART NO:	THREAD




CABLE ENTRY Ø11.0 MAX.



HOOD INTERNAL VIEW



OPTION 1*



OPTION 2*

* Hood can be of either Option 1 or Option 2


Amphenol
FCI

© 2016 AFCl

"This LF product meets European Union Directives and other country regulations as described in GS-47-0004"

Packaging as per GS-14-920

MATERIALS:
1.ABS UNFILLED UL 94 HB
(STANDARD)
2.TEMP RANGE -55°C TO +85°C

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB									
ltr	ecn no	dr	date	tolerances unless		otherwise specified				title CONNECTOR HOOD 25 POSITION									
E	I06-0074	MINI	2006/06/08	angles	linear			MM											
F	I10-0122	AMR	2010/05/29			.00±0.1													
G	I10-0231	AMR	2010/11/27	0°±1°				scale NTS											
H	ELX-I-15622	MP	2013/08/24	dr	MINI K VANDANATH	1995/24/03				dwg no				sheet 1 of 1				size	
J	ELX-I-21747	MP	2015/08/22	engr	MITHUN PAUL	2016-11-25				C-DSUB-0024				A3					
K	ELX-I-25452	GREGAR	2016-11-25	chr	GREGAR MATHEW	2017-08-12													
L	ELX-I-27699	GREGAR	2017-08-12	appd	BIJU K PAUL	2017-08-12													
sheet index		revision sheet		L															