

PW 403409 T



Sample image

Order symbol : PW 403409 T

EAN : 6418074320476

Product nr : 4901904

Description : PW Inspection Protection window,

Remarks : 394x346x88 mm, DB3 lock, Transparent cover

4901904_FIBOX_PW_403409_T DIM

Dimensions :	Height	Width	Depth
mm :	394	346	88

Materials :

Material : Polycarbonate

Temperatures :

Temperature °C (continuous) : -40 ... 80
Temperature °F (continuous) : -40 ... 175

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK09;
electrical_insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C
NEMA Class	NEMA 4, 4X, 12 and 13