

Han Q 8/0-agg vernickelt



Part number	09 12 008 0303
Specification	Han Q 8/0-agg vernickelt
HARTING eCatalogue	https://b2b.harting.com/09120080303

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Bulkhead mounted housings

Version

Locking type	Single locking lever
Size	Han-Compact®
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------



Pushing Performance

Commercial data

Packaging size	10
Net weight	61.9 g
Country of origin	Germany
Customs tariff number	85389099