

## Han Q 8/0-kg-Adaptalock



Part number	09 12 008 0728
Specification	Han Q 8/0-kg-Adaptalock
HARTING eCatalogue	<a href="https://b2b.harting.com/09120080728">https://b2b.harting.com/09120080728</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Cable to cable housing
Description of hood/housing	for flexible conduits Adaptaflex PAFS18

### Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Top entry
Cable entry	1x PAFS 18
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Polyamide
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	31.3 g
Country of origin	Germany
Customs tariff number	85389099