

Han Q 8/0 ABDECKKAPPE



Part number	09 12 008 5407
Specification	Han Q 8/0 ABDECKKAPPE
HARTING eCatalogue	https://b2b.harting.com/09120085407

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Protection cover
Description of hood/ housing	for bulkhead mounted housings Thermoplastic

Version

Locking type	Single locking lever
Size	Han-Compact®
Field of application	Hoods/housings for industrial applications
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076



Pushing Performance

Specifications and approvals

CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	8.76 g
Country of origin	Germany
Customs tariff number	85389099
