

Han-Modular coax F-contact 50Ohm (RG58)



| | |
|--------------------|---|
| Part number | 09 14 000 6215 |
| Specification | Han-Modular coax F-contact 50Ohm (RG58) |
| HARTING eCatalogue | https://b2b.harting.com/09140006215 |

Identification

| | |
|--|-----------------|
| Category | Contacts |
| Series | D-Sub |
| Type of contact | Coaxial contact |
| Description of the contactfor cables RG 58 | |

Version

| | |
|--------------------|-----------------------------|
| Termination method | Solder / solder termination |
| Gender | Male |

Technical characteristics

| | |
|--------------------|----------------------|
| Operating current | ≤ 1.5 A |
| Contact resistance | ≤ 10 m Ω |
| Impedance | 50 Ω |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | EN 60664-1 |
|----------------|------------|



Pushing Performance

Specifications and approvals

| |
|-----------|
| IEC 61984 |
|-----------|

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 10 |
| Net weight | 2.8 g |
| Country of origin | Germany |
| Customs tariff number | 85366910 |