

Han-Modular ECO agg IP65 (without PE)



Part number	09 14 001 0320
Specification	Han-Modular ECO agg IP65 (without PE)
HARTING eCatalogue	https://b2b.harting.com/09140010320

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular [®] ECO
Type of hood/housing	Bulkhead mounted housings

Version

Locking type	Snap-in latches
Size	Modular ECO

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------



Pushing Performance

Commercial data

Packaging size	2
Net weight	14.22 g
Country of origin	Germany
Customs tariff number	85389099