


Han 200A crimp module, male



Part number	09 14 001 3001
Specification	Han 200A crimp module, male
HARTING eCatalogue	https://b2b.harting.com/09140013001

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® 200 A module

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	1
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	25 ... 70 mm²
Electrical data acc. to IEC 61984	200 A 1,000 V 8 kV 3
Rated current	200 A
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 PVVA8.E318390

Commercial data

Packaging size	1
Net weight	18.9 g
Country of origin	Germany
Customs tariff number	85389099