

## Han 3 Quintax-M-c



Part number	09 15 003 3001
Specification	Han 3 Quintax-M-c
HARTING eCatalogue	<a href="https://b2b.harting.com/09150033001">https://b2b.harting.com/09150033001</a>

### Identification

Category	Inserts
Series	Han-Brid <sup>®</sup>
Identification	Han-Brid <sup>®</sup> Quintax 3 A

### Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	1
	4
	8
Additional contacts	+ shielding + 2 power contacts
Details	Please order contacts separately.

### Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Insulation resistance	≥10 <sup>10</sup> Ω
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	10
Net weight	8.22 g
Country of origin	Germany
Customs tariff number	85389099