

5

4

3


2

1

D



C

B



vorverrastet
pre assembled
preassemble

verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 1 des Flachkabels
1) Contact no.1, 1st wire of flat cable
1) Contact no.1, repère 1 du câble

A

0918 506 5803 58U	0,76 μm Au	Bulk packaging MOQ = 5000 pcs		All Dimensions in mm Original Size DIN A 4			Techn. Character.				Nicht tolerierte Masse/ <i>Free size tolerances</i>				
0918 506 6803 58U	2														
0918 506 7803 58U	3														
0918 506 5803	0,76 μm Au	N.A.						Dat.	Name	Massstab/ <i>Scale</i> 2:1	SEK 18 Female connector 6 poles with central polarisation cover without cable stop				
0918 506 6803	2	N.A.					Detail.	01-FEB-00	Th						
0918 506 7803	3	N.A.					Insp.								
			33797	10/08/06	PK	Stand.									
Bestell-Nr. <i>Part-No.</i> Reference	Anforderungsstufe <i>Performance level</i> Niveau de qualite	Index Designation	33788	21/07/06	PK	HARTING EURL F-95972 Paris					TB 09 18 506 X803				Blatt/ <i>page</i> 1/1
			26570	01-FEB-00	JB										
			Mod.	Dat.	Name										