

Han Q 8/0-kg-M25



Part number	19 12 008 0729
Specification	Han Q 8/0-kg-M25
HARTING eCatalogue	https://b2b.harting.com/19120080729

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Cable to cable housing
Description of hood/housing	for Han-Compact® half cable gland

Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Top entry
Cable entry	1x M25
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Polyamide
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	29.1 g
Country of origin	Germany
Customs tariff number	85389099