

## Han-Modular Compact side entry M25



Part number	19 14 001 0501
Specification	Han-Modular Compact side entry M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19140010501">https://b2b.harting.com/19140010501</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Hoods

### Version

Locking type	Single locking lever
Size	Modular Compact
Version	Side entry
Cable entry	1x M25
Pack contents	4 screws are included within the delivery

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque	1 Nm Fixing screws M3
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 in locked position

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Commercial data

Packaging size	10
----------------	----



Pushing Performance

## Commercial data

Net weight	89.75 g
Country of origin	Germany
Customs tariff number	85389099