

## Han INOX 10B-HSE-R-M32



Part number	19 44 310 0547
Specification	Han INOX 10B-HSE-R-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19443100547">https://b2b.harting.com/19443100547</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Hoods

### Version

Locking type	Single locking lever
Size	10 B
Version	Side entry
Cable gland	1x M32
Field of application	Hoods/housings for harsh environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	746.2 g
Country of origin	Germany
Customs tariff number	85389099