




Pushing Performance

Acces. Special Cable Clamp EMC M20



Part number	19 62 000 5082
Specification	Acces. Special Cable Clamp EMC M20
HARTING eCatalogue	https://b2b.harting.com/19620005082

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Wrench size	A/F 22
Degree of protection acc. to IEC 60529	IP68
Size	M20
Clamping range	7 ... 10.5 mm
Shielding diameter	6.5 ... 10.5 mm
Width across corners	24.4 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Commercial data

Packaging size	10
Net weight	33.36 g
Country of origin	Germany



Pushing Performance

Commercial data

Customs tariff number	84849000
-----------------------	----------
