

Data Sheet

Stainless Steel Ties



Technical data

BN	Length (in mm)	Width (in mm)	Lock measurements (W/L/H)	Min./Max. Bundle diameter (in mm)	Temperature range (°C)	Tensile strength (N)	Content	Material	Color
3161889	200	4.6	6.5/11.3/4.6	15/61.9	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161890	290	4.6	6.5/11.3/4.6	15/90.6	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161891	360	4.6	6.5/11.3/4.6	15/112.8	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161892	520	4.6	6.5/11.3/4.6	15/163.8	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161893	680	4.6	6.5/11.3/4.6	15/214.8	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161894	840	4.6	6.5/11.3/4.6	15/265.7	-80 ~ +300	890.0	100 pcs	AISI 304	Silver
3161895	200	7.9	10/13.7/5.7	15/61.9	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3164847	290	7.9	10/13.7/5.7	15/90.6	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3164134	360	7.9	10/13.7/5.7	15/112.8	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3161896	520	7.9	10/13.7/5.7	15/163.8	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3161897	680	7.9	10/13.7/5.7	15/214.8	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3164135	840	7.9	10/13.7/5.7	15/265.7	-80 ~ +300	1600.0	100 pcs	AISI 304	Silver
3161898	200	4.6	6.5/11.3/4.6	15/61.9	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3164136	290	4.6	6.5/11.3/4.6	15/90.6	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3164137	360	4.6	6.5/11.3/4.6	15/112.8	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3161899	520	4.6	6.5/11.3/4.6	15/163.8	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3161900	680	4.6	6.5/11.3/4.6	15/214.8	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3161901	840	4.6	6.5/11.3/4.6	15/265.7	-40 ~ +150	450.0	100 pcs	Coated AISI 304	Black
3161902	200	7.9	10/13.7/5.7	15/61.9	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black
3161903	290	7.9	10/13.7/5.7	15/90.6	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black
3161904	360	7.9	10/13.7/5.7	15/112.8	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black
3161905	520	7.9	10/13.7/5.7	15/163.8	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black
3161906	680	7.9	10/13.7/5.7	15/214.8	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black
3161907	840	7.9	10/13.7/5.7	15/265.7	-40 ~ +150	800.0	100 pcs	Coated AISI 304	Black

Data Sheet

BN	Length (in mm)	Width (in mm)	Lock measurements (W/L/H)	Min./Max. Bundle diameter (in mm)	Temperature range (°C)	Tensile strength (N)	Content	Material	Color
3161908	200	4.6	6.5/11.3/4.6	15/61.9	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3161909	290	4.6	6.5/11.3/4.6	15/90.6	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3164138	360	4.6	6.5/11.3/4.6	15/112.8	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3164139	520	4.6	6.5/11.3/4.6	15/163.8	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3164140	680	4.6	6.5/11.3/4.6	15/214.8	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3164141	840	4.6	6.5/11.3/4.6	15/265.7	-80 ~ +300	890.0	100 pcs	AISI 316	Silver
3164142	200	7.9	10/13.7/5.7	15/61.9	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164143	290	7.9	10/13.7/5.7	15/90.6	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164144	360	7.9	10/13.7/5.7	15/112.8	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164145	520	7.9	10/13.7/5.7	15/163.8	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164146	680	7.9	10/13.7/5.7	15/214.8	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164147	840	7.9	10/13.7/5.7	15/265.7	-80 ~ +300	1600.0	100 pcs	AISI 316	Silver
3164148	200	4.6	6.5/11.3/4.6	15/61.9	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164149	290	4.6	6.5/11.3/4.6	15/90.6	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164150	360	4.6	6.5/11.3/4.6	15/112.8	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164151	520	4.6	6.5/11.3/4.6	15/163.8	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164152	680	4.6	6.5/11.3/4.6	15/214.8	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164153	840	4.6	6.5/11.3/4.6	15/265.7	-40 ~ +150	450.0	100 pcs	Coated AISI 316	Black
3164154	200	7.9	10/13.7/5.7	15/61.9	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164155	290	7.9	10/13.7/5.7	15/90.6	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164156	360	7.9	10/13.7/5.7	15/112.8	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164157	520	7.9	10/13.7/5.7	15/163.8	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164158	680	7.9	10/13.7/5.7	15/214.8	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164159	840	7.9	10/13.7/5.7	15/265.7	-40 ~ +150	800.0	100 pcs	Coated AISI 316	Black
3164160	150	4.6	6.5/11.3/4.6	15/46	-80 ~ +300	890.0	10 pcs	AISI 304	Silver
3164161	290	4.6	6.5/11.3/4.6	15/90.6	-80 ~ +300	890.0	10 pcs	AISI 304	Silver
3164162	150	4.6	6.5/11.3/4.6	15/46	-40 ~ +150	450.0	10 pcs	Coated AISI 304	Black
3164163	290	4.6	6.5/11.3/4.6	15/90.6	-40 ~ +150	450.0	10 pcs	Coated AISI 304	Black
3164164	150	4.6	6.5/11.3/4.6	15/46	-80 ~ +300	890.0	10 pcs	AISI 316	Silver
3164165	290	4.6	6.5/11.3/4.6	15/90.6	-80 ~ +300	890.0	10 pcs	AISI 316	Silver
3164166	150	4.6	6.5/11.3/4.6	15/46	-40 ~ +150	450.0	10 pcs	Coated AISI 316	Black
3164167	290	4.6	6.5/11.3/4.6	15/90.6	-40 ~ +150	450.0	10 pcs	Coated AISI 316	Black