

## Cable Management

Order code	Manufacturer code	Description
04-0560	NB12	PK/100 19X19 NATURAL CBL TIE BASE (RC)

Cable Management	Page 1 of 3
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

**To:** \_\_\_\_\_ **From:** \_\_\_\_\_  
**Fax:** \_\_\_\_\_ **Pages:** 1 OF 2  
**Phone:** \_\_\_\_\_ **Date:** 15/05/2007  
**Re:** SPECIFICATION **CC:** FILE

PLEASE FIND BELOW COPY OF UL FILE CARD APPLICABLE TO MATERIAL USED  
ON NATURAL BASES AND ATTACHED ADHESIVE SPECIFICATION FOR BASE.

QMFZ2 Component - Plastics		Wednesday, February 04, 1998				E41938		
<b>E I DUPONT DE NEMOURS &amp; CO INC</b>								
WILMINGTON, DE 19880								
Material Designation: <b>EFEI068</b>								
Product Description: Polyamide 66 (PA66), designated "Zytel" furnished as pellets.								
	<b>Color</b>	<b>Min. Thk.</b>	<b>Flame Class</b>	<b>HWI</b>	<b>HAI</b>	<b>RTI Elec</b>	<b>RTI Imp</b>	<b>RTI Str</b>
<b>ALL</b>		0.71	V-2	4	0	125	65	65
		1.5	V-2	3	0	125	75	85
		3.0	V-2	2	0	125	75	85
		6.0	V-2	2	0	125	75	85
					<b>CTI 0</b>	<b>HVTR: 0</b>	<b>D495:6</b>	
NOTE -Material designations that are color pigmented may be followed by suffix letters and numbers.								
Report Date: 07/29/1996			<b>Underwriters Laboratories Inc ®</b>				324299-147	
UL94 small-scale test data does not pertain to building materials, furnishings and related contents. UL 94 small-scale test data is intended solely for determining the flammability of plastic materials used in components and parts of end-product devices and appliances, where the acceptability of the combination is determined by ULI.								

### Product Description

Double Sided White Polyethylene foam with a synthetic rubber resin adhesive

### Product Advantages

Highly Conformable Foam with very high sheer strength as well as having a versatile adhesive which offers high adhesion and cohesion suitable for bonding most substrates including contoured surfaces.

### Technical Data

Carrier:	: Closed cell polyethylene foam.
Colour:	: White.
Adhesive:	: Synthetic rubber resin.
Thickness:	: 0.8mm
Liner:	: White Paper.
Adhesive Power:	: 20°C 25
AFERA 4012 N/25mm	: 70°C 5.
Adhesive Sheer:	: 20°C 120.
AFERA 4012 N/25mm	: 70°C 2.
Temperature Range:	: -10°C +60°C.
Chemical Resistance:	: Water, Alcohols and Detergents.

### Comments

A specially formed performance double sided tape with the obvious advantages of an aggressive rubber based adhesive. This extremely versatile mounting tape finds its home in fixing all manner of plastic articles for both point of sale display and body assembly but, its prime function in life is the mounting of full length mirrors in furniture decoration.

#### **IMPORTANT:**

This information is based on our best current knowledge and is intended as a general guide to product performance. It is not a warranty or specification and customers must determine that the product is suitable for their particular purposes before use.