

# Data Sheet

## Metal Barb Cable Ties, 100 pcs



### Technical data

Flammability rating: UL94 V2

Plenum rated: AH-2

Operating temperature: -60 °C ~ 85 °C

Storage relative humidity: 50 %

Min. installation temperature: -20 °C

BN	Length (in mm)	Width (in mm)	Lock measurements (W/L/H)	Thickness of cable tie	Min./Max. Bundle diameter (in mm)	Tensile strength (LBS)	Newton (N)	Color
3203536	100	3	5.9/4.5/4	1.1	3/20.5	18	80	Natural
3203537	140	3.6	6/5/4	1.25	3.5/33.0	40	180	Natural
3203538	200	4.8	8.25/6/5.5	1.25	3.5/49.5	50	222	Natural
3203539	300	4.8	8.25/6/5.5	1.25	3.5/81.0	50	222	Natural
3203540	370	4.8	8.25/6/5.5	1.25	3.5/103.5	50	222	Natural
3203545	370	7	12.9/9/8.2	1.7	8.5/103.5	120	540	Natural
3203546	100	3	5.9/4.5/4	1.1	3/20.5	18	80	Black
3203535	140	3.6	6/5/4	1.25	3.5/33.0	40	180	Black
3203547	200	4.8	8.25/6/5.5	1.25	3.5/49.5	50	222	Black
3203548	300	4.8	8.25/6/5.5	1.25	3.5/81.0	50	222	Black
3203549	370	4.8	8.25/6/5.5	1.25	3.5/103.5	50	222	Black
3203550	370	7	12.9/9/8.2	1.7	8.5/103.5	120	540	Black