

Data Sheet

Screw Mounted Cable Ties, 100 pcs



Technical data

Flammability rating: UL94 V2

Plenum rated: AH-2

Operating temperature: -40 °C ~ 85 °C

Storage relative humidity: 50 %

Min. installation temperature: -10 °C

BN	Length (in mm)	Width (in mm)	Lock measurements (W/L/H)	Thickness of cable tie	Min./Max. Bundle diameter (in mm)	Tensile strength (LBS)	Newton (N)	Color
3203551	200	4.8	7.8/20/5.2	1.2	3/49.8	50	222	Natural
3203541	370	4.8	7.8/20/5.2	1.2	3/103.8	50	222	Natural
3203542	400	7.6	13.5/28.4/7.6	1.75	8/109.2	120	540	Natural
3203552	200	4.8	7.8/20/5.2	1.2	3/49.8	50	222	Black
3203543	370	4.8	7.8/20/5.2	1.2	3/103.8	50	222	Black
3203544	400	7.6	13.5/28.4/7.6	1.75	8/109.2	120	540	Black