

Product Code: QCGM40TPW

Description: Nylon 40mm Meter Tail Glands With Plug - White



**Dimensions**

Spanner Size (mm)	49
Threaded Diameter (mm)	40
Threaded Entry Length (mm)	18.4

**General Information**

Colour	White (RAL 9003)
Suitable Cable Size (mm <sup>2</sup> )	Line & Neutral: 25CPC: 16 (Plug Provided if No CPC Available)
Recommended Cap Tightening Torque (Nm)	5.5
Ingress Protection	IP68
Temperature Rating (°C)	0 to +80

**Materials**

Gland Body: Nylon 66  
 Seal: TPE (Thermoplastic Elastomer)  
 Washer: PVC (Polyvinyl Chloride)

**Standards**

ANSI/UL 514B  
 BS EN 60529: 1992 + A2: 2013

