

Product Code: QCGM32TPW

Description: Nylon 32mm Meter Tail Glands With Plug - White

**Dimensions**

Spanner Size (mm)	42
Threaded Diameter (mm)	32
Threaded Entry Length (mm)	14.7

General Information

Colour	White (RAL 9003)
Suitable Cable Size (mm ²)	Line & Neutral: 25CPC: 16 (Plug Provided if No CPC Available)
Recommended Cap Tightening Torque (Nm)	5
Ingress Protection	IP68
Temperature Rating (°C)	0 to +80

Materials

Gland Body: Nylon 66
Seal: TPE (Thermoplastic Elastomer)
Washer: PVC (Polyvinyl Chloride)

Standards

ANSI/UL 514B
BS EN 60529: 1992 + A2: 2013

