



Materials:

UL approved Nylon 66, 94V-2
High tensile strength with low insertion force
Excellent resistance to weathering and ageing

Feature:

Suitable for a multitude of uses in various industries

Application:

Self-locking for fast and easy application.

Operating Temperature:

-40°C to +85°C



Order code	MPN	Colour	Width W (mm)	Length L (mm)	Max. Bundle Diameter (mm)	Min. Tensile Strength (kg)
04-0867	UNI-CT2-B	Black	3.6	150	36	18
	UNI-CT24-B	Black	3.6	180	46	18
04-0868	UNI-CT20-B	Black	3.6	200	53	18
04-0869	UNI-CT7-B	Black	3.6	292	76	18
04-0870	UNI-CT29-B	Black	3.6	368	105	18
04-0871	UNI-CT2-W	Natural	3.6	150	36	18
	UNI-CT24-W	Natural	3.6	180	46	18
04-0872	UNI-CT20-W	Natural	3.6	200	53	18
04-0873	UNI-CT7-W	Natural	3.6	292	76	18
04-0874	UNI-CT29-W	Natural	3.6	368	105	18