



**Materials:**

UL approved Nylon 66, 94V-2  
High tensile strength with low insertion force  
Excellent resistance to weathering and ageing

**Feature:**

Suitable for a multitude of uses in various industries

**Application:**

Self-locking for fast and easy application.

**Operating Temperature:**

-40°C to +85°C



Order code	MPN	Colour	Width W (mm)	Length L (mm)	Max. Bundle Diameter (mm)	Min. Tensile Strength (kg)
<b>04-0867</b>	UNI-CT2-B	Black	3.6	150	36	18
	UNI-CT24-B	Black	3.6	180	46	18
<b>04-0868</b>	UNI-CT20-B	Black	3.6	200	53	18
<b>04-0869</b>	UNI-CT7-B	Black	3.6	292	76	18
<b>04-0870</b>	UNI-CT29-B	Black	3.6	368	105	18
<b>04-0871</b>	UNI-CT2-W	Natural	3.6	150	36	18
	UNI-CT24-W	Natural	3.6	180	46	18
<b>04-0872</b>	UNI-CT20-W	Natural	3.6	200	53	18
<b>04-0873</b>	UNI-CT7-W	Natural	3.6	292	76	18
<b>04-0874</b>	UNI-CT29-W	Natural	3.6	368	105	18