



Materials:

UL approved Nylon 66, 94V-2
High tensile strength with low insertion force
Excellent resistance to weathering and ageing

Feature:

Suitable for a multitude of uses in various industries

Application:

Self-locking for fast and easy application.

Operating Temperature:

-40°C to +85°C



Cable Ties (Pack 100)

- Standard Range

| Order code | MPN | Colour | Width W (mm) | Length L (mm) | Max. Bundle Diameter (mm) | Min. Tensile Strength (kg) |
|----------------|------------|---------|--------------|---------------|---------------------------|----------------------------|
| | UNI-CT25-B | Black | 4.8 | 120 | 27 | 22 |
| 04-0875 | UNI-CT3-B | Black | 4.8 | 160 | 39 | 22 |
| | UNI-CT49-B | Black | 4.8 | 190 | 50 | 22 |
| 04-0876 | UNI-CT5-B | Black | 4.8 | 203 | 52 | 22 |
| 04-0877 | UNI-CT26-B | Black | 4.8 | 250 | 68 | 22 |
| | UNI-CT30-B | Black | 4.8 | 280 | 77 | 22 |
| 04-0878 | UNI-CT8-B | Black | 4.8 | 300 | 83 | 22 |
| 04-0879 | UNI-CT10-B | Black | 4.8 | 368 | 105 | 22 |
| | UNI-CT31-B | Black | 4.8 | 385 | 110 | 22 |
| 04-0880 | UNI-CT12-B | Black | 4.8 | 432 | 125 | 22 |
| | UNI-CT54-B | Black | 4.8 | 450 | 131 | 22 |
| | UNI-CT55-B | Black | 4.8 | 500 | 147 | 22 |
| | UNI-CT32-B | Black | 4.8 | 550 | 162 | 22 |
| | UNI-CT33-B | Black | 4.8 | 635 | 189 | 22 |
| | UNI-CT51-B | Black | 4.8 | 730 | 216 | 22 |
| | UNI-CT25-W | Natural | 4.8 | 120 | 27 | 22 |
| 04-0881 | UNI-CT3-W | Natural | 4.8 | 160 | 39 | 22 |
| | UNI-CT49-W | Natural | 4.8 | 190 | 50 | 22 |
| 04-0882 | UNI-CT5-W | Natural | 4.8 | 203 | 52 | 22 |
| 04-0883 | UNI-CT26-W | Natural | 4.8 | 250 | 68 | 22 |
| | UNI-CT30-W | Natural | 4.8 | 280 | 77 | 22 |
| 04-0884 | UNI-CT8-W | Natural | 4.8 | 300 | 83 | 22 |
| 04-0885 | UNI-CT10-W | Natural | 4.8 | 368 | 105 | 22 |
| | UNI-CT31-W | Natural | 4.8 | 385 | 110 | 22 |
| 04-0886 | UNI-CT12-W | Natural | 4.8 | 432 | 125 | 22 |
| | UNI-CT54-W | Natural | 4.8 | 450 | 131 | 22 |
| | UNI-CT55-W | Natural | 4.8 | 500 | 147 | 22 |
| | UNI-CT32-W | Natural | 4.8 | 550 | 162 | 22 |
| | UNI-CT33-W | Natural | 4.8 | 635 | 189 | 22 |