



Materials:

UL approved Nylon 66, 94V-2
High tensile strength with low insertion force
Excellent resistance to weathering and ageing

Feature:

Suitable for a multitude of uses in various industries

Application:

Self-locking for fast and easy application.

Operating Temperature:

-40°C to +85°C



| Order code | MPN | Colour | Width W (mm) | Length L (mm) | Max. Bundle Diameter (mm) | Min. Tensile Strength (kg) |
|----------------|------------|---------|--------------|---------------|---------------------------|----------------------------|
| | UNI-CT27-B | Black | 7.6 | 150 | 32 | 55 |
| 04-0887 | UNI-CT6-B | Black | 7.6 | 200 | 52 | 55 |
| | UNI-CT34-B | Black | 7.6 | 240 | 65 | 55 |
| 04-0888 | UNI-CT9-B | Black | 7.6 | 300 | 80 | 55 |
| 04-0889 | UNI-CT11-B | Black | 7.6 | 370 | 101 | 55 |
| 04-0890 | UNI-CT35-B | Black | 8.0 | 450 | 128 | 55 |
| 04-0891 | UNI-CT36-B | Black | 8.0 | 550 | 160 | 55 |
| 04-0892 | UNI-CT37-B | Black | 7.6 | 750 | 218 | 55 |
| | UNI-CT46-B | Black | 9.0 | 270 | 74 | 80 |
| | UNI-CT15-B | Black | 9.0 | 450 | 128 | 80 |
| 04-0893 | UNI-CT16-B | Black | 9.0 | 550 | 160 | 80 |
| | UNI-CT40-B | Black | 9.0 | 609 | 177 | 80 |
| | UNI-CT14-B | Black | 9.0 | 710 | 209 | 80 |
| 04-0894 | UNI-CT21-B | Black | 9.0 | 762 | 227 | 80 |
| | UNI-CT50-B | Black | 9.0 | 812 | 243 | 80 |
| | UNI-CT41-B | Black | 9.0 | 914 | 275 | 80 |
| | UNI-CT19-B | Black | 9.0 | 1168 | 356 | 80 |
| | UNI-CT42-B | Black | 9.0 | 1219 | 372 | 80 |
| | UNI-CT48-B | Black | 9.0 | 1500 | 462 | 80 |
| | UNI-CT27-W | Natural | 7.6 | 150 | 32 | 55 |
| 04-0895 | UNI-CT6-W | Natural | 7.6 | 200 | 52 | 55 |
| | UNI-CT34-W | Natural | 7.6 | 240 | 65 | 55 |
| 04-0896 | UNI-CT9-W | Natural | 7.6 | 300 | 80 | 55 |
| 04-0897 | UNI-CT11-W | Natural | 7.6 | 370 | 101 | 55 |
| 04-0898 | UNI-CT35-W | Natural | 8.0 | 450 | 128 | 55 |
| 04-0899 | UNI-CT36-W | Natural | 8.0 | 550 | 160 | 55 |
| 04-0900 | UNI-CT37-W | Natural | 7.6 | 750 | 218 | 55 |
| | UNI-CT15-W | Natural | 9.0 | 450 | 128 | 80 |
| 04-0901 | UNI-CT16-W | Natural | 9.0 | 550 | 160 | 80 |
| | UNI-CT40-W | Natural | 9.0 | 609 | 177 | 80 |
| | UNI-CT14-W | Natural | 9.0 | 710 | 209 | 80 |
| 04-0902 | UNI-CT21-W | Natural | 9.0 | 762 | 227 | 80 |
| | UNI-CT50-W | Natural | 9.0 | 812 | 243 | 80 |
| | UNI-CT41-W | Natural | 9.0 | 914 | 275 | 80 |
| | UNI-CT19-W | Natural | 9.0 | 1168 | 356 | 80 |
| | UNI-CT42-W | Natural | 9.0 | 1219 | 372 | 80 |
| | UNI-CT48-W | Natural | 9.0 | 1500 | 462 | 80 |