




Coloured Cable Ties (Pack 100) – Standard Range

**Materials:**

UL approved Nylon 66, 94V-2
High tensile strength with low insertion force
Excellent resistance to weathering and ageing

Feature:

Suitable for a multitude of uses in various industries

Application:

Self-locking for fast and easy application.

Operating Temperature:

–40°C to +85°C



Coloured Cable Ties (Pack 100) – Standard Range

Order code	MPN	Colour	Width W (mm)	Length L (mm)	Max. Bundle Diameter (mm)	Min. Tensile Strength (kg)
04-0906	UNI-CT5-BLUE	Blue	4.8	203	52	22
04-0905	UNI-CT5-BROWN	Brown	4.8	203	52	22
04-0907	UNI-CT5-GREEN	Green	4.8	203	52	22
	UNI-CT5-ORANGE	Orange	4.8	203	52	22
	UNI-CT5-PURPLE	Purple	4.8	203	52	22
04-0908	UNI-CT5-RED	Red	4.8	203	52	22
	UNI-CT5-SILVER	Silver	4.8	203	52	22
04-0909	UNI-CT5-YELLOW	Yellow	4.8	203	52	22
04-0911	UNI-CT8-BLUE	Blue	4.8	300	83	22
04-0910	UNI-CT8-BROWN	Brown	4.8	300	83	22
04-0912	UNI-CT8-GREEN	Green	4.8	300	83	22
	UNI-CT8-ORANGE	Orange	4.8	300	83	22
	UNI-CT8-PURPLE	Purple	4.8	300	83	22
04-0913	UNI-CT8-RED	Red	4.8	300	83	22
	UNI-CT8-SILVER	Silver	4.8	300	83	22
04-0914	UNI-CT8-YELLOW	Yellow	4.8	300	83	22
	UNI-CT10-BLUE	Blue	4.8	368	105	22
	UNI-CT10-BROWN	Brown	4.8	368	105	22
	UNI-CT10-GREEN	Green	4.8	368	105	22
	UNI-CT10-ORANGE	Orange	4.8	368	105	22
	UNI-CT10-PURPLE	Purple	4.8	368	105	22
	UNI-CT10-RED	Red	4.8	368	105	22
	UNI-CT10-SILVER	Silver	4.8	368	105	22
	UNI-CT10-YELLOW	Yellow	4.8	368	105	22