

Technical Data



Material: Polyvinyl Chloride (PVC)

Colours: grey

Specification	Typical value*	Test method
Thickness	: 0.15 mm	ASTM D1000
Tensile Strength	: 18 N /cm	ASTM D1000
Elongation	: 150 %	ASTM D1000
Adhesion to Steel	: 1,5 N / cm	ASTM D1000
Operating Temperature	: -10°C - 90°C	
Length	: 46 m	
Width	: 51 mm	