

H-2(Z)

Thin-wall heat shrink tubing / flexible / flame retardant / 2:1

Features:

- Crosslinked Polyolefin
- Shrink ratio: 2:1
- Flame retardant
- General purpose
- High flexibility
- UV resistant (according to ISO 8580 test report)

Approvals:

- UL224 125 °C VW-1 600 V file E204071
- CSA file no.: 1934614
- Meets: RoHS, Sony-SS-00259

Application:

- Operating temperature: -55 °C to +125 °C
- Minimum shrink temperature: +70 °C
- Minimum full recovery temperature: +100 °C
- Longitudinal change: 0 ± 10% max.

Order information:

- Colors: black, red, blue, yellow, green, white, purple, brown, orange, grey
- Other colors are available on request
- Also available in various lengths and in mini boxes



This type of heat shrink tubing is available with print (logo/text). Pre-cut lengths are available on request. Contact us for the possibilities.

Type / Size	As supplied: inside diameter in mm (min.)	After recovery: inside diameter in mm (max.)	After recovery: wall thickness in mm (min.)	Reel / Meter
H-2(Z) 1,2/0,6	1,2	0,6	0,33	150
H-2(Z) 1,6/0,8	1,6	0,8	0,36	150
H-2(Z) 2,4/1,2	2,4	1,2	0,44	150
H-2(Z) 3,2/1,6	3,2	1,6	0,44	150
H-2(Z) 4,8/2,4	4,8	2,4	0,51	75
H-2(Z) 6,4/3,2	6,4	3,2	0,56	75
H-2(Z) 9,5/4,8	9,5	4,8	0,56	75
H-2(Z) 12,7/6,4	12,7	6,4	0,65	50
H-2(Z) 16,0/8,0	16,0	8,0	0,69	50
H-2(Z) 19,0/9,5	19,0	9,5	0,80	30
H-2(Z) 25,4/12,7	25,4	12,7	0,90	30
H-2(Z) 32,0/16,0	32,0	16,0	0,90	30
H-2(Z) 38,1/19,0	38,1	19,0	1,00	30
H-2(Z) 50,8/25,4	50,8	25,4	1,00	30
H-2(Z) 76,2/38,1	76,2	38,1	1,20	15
H-2(Z) 102,0/50,8	102,0	50,8	1,30	15
H-2(Z) 126,0/63,5	126,0	63,5	1,30	15
H-2(Z) 150,0/76,0	150,0	76,0	1,30	15