

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009501061](#)
Status: **Active**
Overview: [SPOX Connector System](#)
Description: 3.96mm Pitch SPOX Crimp Housing, Female, with Friction Ramp, 6 Circuits, Natural

Documents:	
3D Model	Product Specification PS-5195-005-001 (PDF)
3D Model (PDF)	Product Specification PS-5273-003-001 (PDF)
Drawing (PDF)	Product Specification PS-5273-004-001 (PDF)
Product Specification PS-5195-003-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5195
Application	Signal, Wire-to-Board
Overview	SPOX Connector System
Product Name	SPOX
UPC	800753534452
Physical	
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1127.900/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5195-06
Reference - Drawing Numbers	
Product Specification	PS-5195-003-001, PS-5195-005-001, PS-5273-003-001, PS-5273-004-001
Sales Drawing	SD-5195-N-020



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[5195 Series](#)

Mates With
[5272](#) , [5273](#) , [5274](#) , [5096](#) , [53405](#) , [5271](#)

Use With
[5194](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION