

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010011034

Status:

Active

Overview:

KK 508 Connector System

Description:

5.08mm Pitch KK Crimp Terminal Housing, 3 Circuits, Natural

Documents:	
<u>3D Model</u>	<u>Product Specification PS-99020-0087-001 (PDF)</u>
<u>Drawing (PDF)</u>	<u>Packaging Specification 30010001-PK-000 (PDF)</u>
<u>3D Model (PDF)</u>	<u>RoHS Certificate of Compliance (PDF)</u>

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>3001</u>
Application	Power, Wire-to-Board
Overview	<u>KK 508 Connector System</u>
Product Name	KK 508
UPC	800753613065

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.925/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	WAVE
-----------------------------	------

Material Info

Engineering Number	3001-03
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	30010001-PK-000
Product Specification	PS-99020-0087-001
Sales Drawing	SDE-3001-N-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

3001 Series

Mates With

Headers 3061 , 3003 , 3061

Use With

Crimp Terminals 2478 , 2578 , 2878

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION