

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200270070

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 0.25mm² PVC Cable, 10.0m (32.81') Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120027
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	883906102449
Physical	
Cable Diameter	4.70mm (.185")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	360.837/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	403000E02M100
Reference - Drawing Numbers	
Sales Drawing	1200860594-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120027 Series

This document was generated on 08/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION